

PRODUCT INFORMATION

MAXTECH

UAR 080X38-Ø12 HL44,4 7001/7015

EAN 4031582323085  
Order number 00007010



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Roller bearing
Wheel color	Silver gray (RAL7001)
Threadguards	Without threadguard
Diameter	3.15 in
Tread width	1.5 in
Axle hole diameter	0.47 in
Hub length	1.75 in
Body width	1.5 in
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Maxtech
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	330.69 lb
Load capacity Static	661.39 lb
Temperature range (Minimum)	-13 °F
Temperature range (Maximum)	176 °F
Overall weight	0.42 lb

# MAXTECH

UAR 080X38-Ø12 HL44,4 7001/7015

EAN 4031582323085  
Order number 00007010



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

