

MAXTECH

UAR 080X38-Ø12 HL44,4 7001/7015

EAN 4031582323085

Broj porudžbine 00007010



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	poliamid
materijal omotaca	Poliuretan, liveno
Nošenje	kotrljajući lezaj
Boja Tocak	Srebrna siva (RAL7001)
stitnici omotaca	Bez stražara
Prečnik	80 mm
Širina omotac	38 mm
dimenzija rupa osovina	12 mm
dužina glavcine	44,4 mm
Širina tela	38 mm
Teškoća gazećeg omotac (A)	92 Šor A
Teškoća gazećeg omotac (D)	42 Šor D

PERFORMANSE

Performanse kotrljanja	● ● ● ○ ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ● ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Maxtech
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	150 kg
Statički Nosivost	300 kg
Temperaturni opseg (Minimalno)	-25 °C
Opseg temperature (maksimalni)	80 °C
Ukupna težina	0,192 kg

MAXTECH

UAR 080X38-Ø12 HL44,4 7001/7015

EAN 4031582323085
Broj porudžbine 00007010



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

