

# MAXTECH

UAR 125X32-Ø12 HL44,4

EAN 4031582323146  
Order number 00007012



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

|                       |                        |
|-----------------------|------------------------|
| Body material         | Polyamide              |
| Tread material        | Polyurethane, injected |
| Bearing               | Roller bearing         |
| Wheel color           | Blue gray (RAL7031)    |
| Threadguards          | Without threadguard    |
| Diameter              | 4.92 in                |
| Tread width           | 1.26 in                |
| Axle hole diameter    | 0.47 in                |
| Hub length            | 1.75 in                |
| Body width            | 1.26 in                |
| Hardness of tread (A) | 92 Shore A             |
| Hardness of tread (D) | 42 Shore D             |

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product name                | Maxtech                       |
| Standard                    | EN12532 - Transport Equipment |
| Load capacity at 4 km/h     | 440.92 lb                     |
| Load capacity Static        | 881.85 lb                     |
| Temperature range (Minimum) | -13 °F                        |
| Temperature range (Maximum) | 176 °F                        |
| Overall weight              | 0.6 lb                        |

# MAXTECH

UAR 125X32-Ø12 HL44,4

EAN 4031582323146  
Order number 00007012



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

