

MAXTECH

UAR 125X32-Ø12 HL44,4

EAN 4031582323146

Broj porudžbine 00007012



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	poliamid
materijal omotaca	Poliuretan, liveno
Nošenje	kotrljajući lezaj
Boja Tocak	Plava siva (RAL7031)
stitnici omotaca	Bez stražara
Prečnik	125 mm
Širina omotac	32 mm
dimenzija rupa osovina	12 mm
dužina glavcine	44,4 mm
Širina tela	32 mm
Teškoća gazećeg omotac (A)	92 Šor A
Teškoća gazećeg omotac (D)	42 Šor D

PERFORMANSE

Performanse kotrljanja	● ● ● ○ ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ● ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Maxtech
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	200 kg
Statički Nosivost	400 kg
Temperaturni opseg (Minimalno)	-25 °C
Opseg temperature (maksimalni)	80 °C
Ukupna težina	0,27 kg

MAXTECH

UAR 125X32-Ø12 HL44,4

EAN 4031582323146

Broj porudžbine 00007012



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

