

# ELASTECH

UEP 200X46-Ø20

EAN 4031582328608  
Order number 00023479



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Polyamide
Tread material	Elastic tire, black, vulcanized
Bearing	Precision ball bearing
Wheel color	Silver grey (RAL7001)
Threadguards	With threadguard
Diameter	200 mm
Tread width	46 mm
Axle hole diameter	20 mm
Hub length	60 mm
Body width	46 mm
Hardness of tread (A)	63 Shore A

## PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Elastech
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	400 kg
Load capacity Static	800 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	80 °C
Overall weight	1.244 kg

# ELASTECH

UEP 200X46-Ø20

EAN 4031582328608  
Order number 00023479



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

