

ELASTECH

UEP 200X46-Ø20

EAN 4031582328608

Broj porudžbine 00023479



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	poliamid
materijal omotaca	Elastična guma, crna, vulkanizovana
Nošenje	precizni kuglicni lezaj
Boja Tocak	Srebrna siva (RAL7001)
stitnici omotaca	Sa threadguard
Prečnik	200 mm
Širina omotac	46 mm
dimenzija rupa osovina	20 mm
dužina glavnice	60 mm
Širina tela	46 mm
Teškoća gazećeg omotac (A)	63 Šora A

PERFORMANSE

Performanse kotrljanja	● ● ● ● ○
Buka u pokretu	● ● ● ● ●
Ishrana	● ● ● ○ ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Elastech
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	400 kg
Statički Nosivost	800 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	80 °C
Ukupna težina	1,244 kg

ELASTECH

UEP 200X46-Ø20

EAN 4031582328608
Broj porudžbine 00023479



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

