

PURETECH

JYX 150X32-Ø8,3 CLIP

EAN 4031582319972
Order number 00024890



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Puretech
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	330.69 lb
Load capacity Static	661.39 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	185 °F
Overall weight	1.97 lb

WHEEL

Body material	Zinc die-cast
Tread material	Solid rubber, black, electric-conductive
Bearing	Precision ball bearing, sealed
Wheel color	Metallic
Threadguards	With threadguard
Diameter	5.91 in
Tread width	1.26 in
Axle hole diameter	0.33 in
Hub length	1.4 in
Body width	1.26 in
Hardness of tread (A)	75 Shore A

HOUSING

Electric conductive	✓
---------------------	---

PURETECH

JYX 150X32-Ø8,3 CLIP

EAN 4031582319972
Order number 00024890



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

