

SUPRATECH

PJR 100X32-Ø12 HL44,4

EAN 4031582320527
Order number 00030822



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Roller bearing
Wheel color	Silver gray (RAL7001)
Threadguards	Without threadguard
Diameter	3.94 in
Tread width	1.26 in
Axle hole diameter	0.47 in
Hub length	1.75 in
Body width	1.26 in
Hardness of tread (A)	87 Shore A

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Supratech
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	176.37 lb
Load capacity Static	352.74 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall weight	0.38 lb

SUPRATECH

PJR 100X32-Ø12 HL44,4

EAN 4031582320527
Order number 00030822



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

