

SUPRATECH

PJR 100X32-Ø12 HL44,4

EAN 4031582320527
Broj porudžbine 00030822

BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja ● ● ● ○ ○

Buka u pokretu ● ● ● ● ○

Ishrana ● ● ● ○ ○

otpornost na rdju ● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Supratech
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	80 kg
Statički Nosivost	160 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	0,171 kg

TOCAK

Materijal za telo	polipropilen
materijal omotaca	Termoplastična guma
Nošenje	kotrljajući lezaj
Boja Tocak	Srebrna siva (RAL7001)
stitnici omotaca	Bez stražara
Prečnik	100 mm
Širina omotac	32 mm
dimenzija rupa osovina	12 mm
dužina glavcine	44,4 mm
Širina tela	32 mm
Teškoća gazećeg omotac (A)	87 Šora A

SUPRATECH

PJR 100X32-Ø12 HL44,4

EAN 4031582320527
Broj porudžbine 00030822



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

