

## BASETECH

POR 108X36-Ø12 HL44,4

EAN 4031582320794  
Broj porudžbine 00030953

BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## PERFORMANSE

Performanse kotrljanja ● ● ● ○ ○

Buka u pokretu ● ● ● ○ ○

Ishrana ● ● ● ● ○

otpornost na rdju ● ● ● ○ ○

## OSNOVNI ATRIBUTI

Naziv proizvoda	Basetech
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	160 kg
Statički Nosivost	320 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	0,154 kg

## TOCAK

Materijal za telo	polipropilen
materijal omotaca	Identično sa telom Tocak
Nošenje	kotrljajući lezaj
Boja Tocak	Grafitna crna (RAL9011)
stitnici omotaca	Bez stražara
Prečnik	108 mm
Širina omotac	36 mm
dimenzija rupa osovina	12 mm
dužina glavcine	44,4 mm
Širina tela	36 mm
Teškoća gazećeg omotac (D)	65 Šor D

# BASETECH

POR 108X36-Ø12 HL44,4

EAN 4031582320794

Broj porudžbine 00030953



BETTER MOBILITY. BETTER LIFE.

## TEHNIČKI CRTEŽI

---

