

# PURETECH

PVR 125X37-Ø12 HL44

EAN 4031582321265  
Broj porudžbine 00030955



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## TOCAK

|                            |                         |
|----------------------------|-------------------------|
| Materijal za telo          | polipropilen            |
| materijal omotaca          | Cvrsta guma crna        |
| Nošenje                    | kotrljajući lezaj       |
| Boja Tocak                 | Grafitna crna (RAL9011) |
| stitnici omotaca           | Bez stražara            |
| Prečnik                    | 125 mm                  |
| Širina omotac              | 37 mm                   |
| dimenzija rupa osovina     | 12 mm                   |
| dužina glavcine            | 44 mm                   |
| Širina tela                | 37 mm                   |
| Teškoća gazećeg omotac (A) | 80 Šešelj A             |

## PERFORMANSE

|                        |           |
|------------------------|-----------|
| Performanse kotrljanja | ● ● ● ○ ○ |
| Buka u pokretu         | ● ● ● ● ○ |
| Ishrana                | ● ● ● ○ ○ |
| otpornost na rdju      | ● ● ● ○ ○ |

## OSNOVNI ATRIBUTI

|                                |                              |
|--------------------------------|------------------------------|
| Naziv proizvoda                | Puretech                     |
| Standard                       | EN12532 - transportna oprema |
| Nosivost na 4 km/h             | 100 kg                       |
| Statički Nosivost              | 200 kg                       |
| Temperaturni opseg (Minimalno) | -20 °C                       |
| Opseg temperature (maksimalni) | 60 °C                        |
| Ukupna težina                  | 0,467 kg                     |

# PURETECH

PVR 125X37-Ø12 HL44

EAN 4031582321265  
Broj porudžbine 00030955



BETTER MOBILITY. BETTER LIFE.

## TEHNIČKI CRTEŽI

---

