

MAXTECH

UAR 100X32-Ø12 HL34,9

EAN 4031582323115
Order number 00030958



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

| | |
|-----------------------|------------------------|
| Body material | Polyamide |
| Tread material | Polyurethane, injected |
| Bearing | Roller bearing |
| Wheel color | Silver grey (RAL7001) |
| Threadguards | Without threadguard |
| Diameter | 100 mm |
| Tread width | 32 mm |
| Axle hole diameter | 12 mm |
| Hub length | 34.9 mm |
| Body width | 32 mm |
| Hardness of tread (A) | 91 Shore A |
| Hardness of tread (D) | 40 Shore D |

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ● ○ |
| Attrition | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|-------------------------------|
| Product name | Maxtech |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 4 km/h | 100 kg |
| Load capacity Static | 200 kg |
| Temperature range (Minimum) | -25 °C |
| Temperature range (Maximum) | 80 °C |
| Overall weight | 0.198 kg |

MAXTECH

UAR 100X32-Ø12 HL34,9

EAN 4031582323115
Order number 00030958



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

