

MAXTECH

UAR 100X32-Ø12 HL34,9

EAN 4031582323115

Broj porudžbine 00030958



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja ● ● ● ○ ○

Buka u pokretu ● ● ● ● ○

Ishrana ● ● ● ○ ○

otpornost na rdju ● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Maxtech
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	100 kg
Statički Nosivost	200 kg
Temperaturni opseg (Minimalno)	-25 °C
Opseg temperature (maksimalni)	80 °C
Ukupna težina	0,198 kg

TOCAK

Materijal za telo	poliamid
materijal omotaca	Poliuretan, liveno
Nošenje	kotrljajući lezaj
Boja Tocka	Srebrna siva (RAL7001)
stitnici omotaca	Bez stražara
Prečnik	100 mm
Širina omotac	32 mm
dimenzija rupa osovina	12 mm
dužina glavnice	34,9 mm
Širina tela	32 mm
Teškoća gazećeg omotac (A)	91 Šor A
Teškoća gazećeg omotac (D)	40 Šor D

MAXTECH

UAR 100X32-Ø12 HL34,9

EAN 4031582323115

Broj porudžbine 00030958



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

