

# ELASTECH

UER 100X34-Ø12

EAN 4031582323290  
Order number 00030961



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Polyamide
Tread material	Elastic tire, black, vulcanized
Bearing	Roller bearing
Wheel color	Silver grey (RAL7001)
Threadguards	Without threadguard
Diameter	100 mm
Tread width	34 mm
Axle hole diameter	12 mm
Hub length	44.4 mm
Body width	34 mm
Hardness of tread (A)	63 Shore A

## PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Elastech
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	160 kg
Load capacity Static	320 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	80 °C
Overall weight	0.245 kg

# ELASTECH

UER 100X34-Ø12

EAN 4031582323290  
Order number 00030961



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

