

# ELASTECH

UER 100X34-Ø12

EAN 4031582323290  
Order number 00030961



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Polyamide
Tread material	Elastic tire, black, vulcanized
Bearing	Roller bearing
Wheel color	Silver gray (RAL7001)
Threadguards	Without threadguard
Diameter	3.94 in
Tread width	1.34 in
Axle hole diameter	0.47 in
Hub length	1.75 in
Body width	1.34 in
Hardness of tread (A)	63 Shore A

## PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Elastech
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	352.74 lb
Load capacity Static	705.48 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	176 °F
Overall weight	0.54 lb

# ELASTECH

UER 100X34-Ø12

EAN 4031582323290  
Order number 00030961



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

