

ELASTECH

UER 100X34-Ø12

EAN 4031582323290
Broj porudžbine 00030961

BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	poliamid
materijal omotaca	Elastična guma, crna, vulkanizovana
Nošenje	kotrljajući lezaj
Boja TocaK	Srebrna siva (RAL7001)
stitnici omotaca	Bez stražara
Prečnik	100 mm
Širina omotac	34 mm
dimenzija rupa osovina	12 mm
dužina glavčine	44,4 mm
Širina tela	34 mm
Teškoća gazećeg omotac (A)	63 Šora A

PERFORMANSE

Performanse kotrljanja	● ● ● ● ○
Buka u pokretu	● ● ● ● ○
Ishrana	● ● ● ○ ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Elastech
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	160 kg
Statički Nosivost	320 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	80 °C
Ukupna težina	0,245 kg

ELASTECH

UER 100X34-Ø12

EAN 4031582323290
Broj porudžbine 00030961



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

