

# ELASTECH

UER 125X40-Ø12

EAN 4031582323306  
Order number 00030962



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Polyamide
Tread material	Elastic tire, black, vulcanized
Bearing	Roller bearing
Wheel color	Silver grey (RAL7001)
Threadguards	Without threadguard
Diameter	125 mm
Tread width	40 mm
Axle hole diameter	12 mm
Hub length	44 mm
Body width	40 mm
Hardness of tread (A)	63 Shore A

## PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Elastech
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	250 kg
Load capacity Static	500 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	80 °C
Overall weight	0.401 kg

# ELASTECH

UER 125X40-Ø12

EAN 4031582323306  
Order number 00030962



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

