

ELASTECH

UER 125X40-Ø12

EAN 4031582323306
Broj porudžbine 00030962

BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	poliamid
materijal omotaca	Elastična guma, crna, vulkanizovana
Nošenje	kotrljajući lezaj
Boja Tocak	Srebrna siva (RAL7001)
stitnici omotaca	Bez stražara
Prečnik	125 mm
Širina omotac	40 mm
dimenzija rupa osovina	12 mm
dužina glavnice	44 mm
Širina tela	40 mm
Teškoća gazećeg omotac (A)	63 Šora A

PERFORMANSE

Performanse kotrljanja	● ● ● ● ○
Buka u pokretu	● ● ● ● ○
Ishrana	● ● ● ○ ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Elastech
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	250 kg
Statički Nosivost	500 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	80 °C
Ukupna težina	0,401 kg

ELASTECH

UER 125X40-Ø12

EAN 4031582323306
Broj porudžbine 00030962



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

