

DURATECH

UOR 125X40-Ø12 HL48,4

EAN 4031582323559
Order number 00030967



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

| | |
|-----------------------|---------------------------|
| Body material | Polyamide |
| Tread material | Identical with wheel body |
| Bearing | Roller bearing |
| Wheel color | Natural white |
| Threadguards | Without threadguard |
| Diameter | 125 mm |
| Tread width | 40 mm |
| Axle hole diameter | 12 mm |
| Hub length | 48.4 mm |
| Body width | 40 mm |
| Hardness of tread (D) | 75 Shore D |

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|-------------------------------|
| Product name | Duratech |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 4 km/h | 300 kg |
| Load capacity Static | 600 kg |
| Temperature range (Minimum) | -25 °C |
| Temperature range (Maximum) | 80 °C |
| Overall weight | 0.272 kg |

DURATECH

UOR 125X40-Ø12 HL48,4

EAN 4031582323559
Order number 00030967



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

