

DURATECH

UOR 125X40-Ø12 HL48,4

EAN 4031582323559

Broj porudžbine 00030967



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	poliamid
materijal omotaca	Identično sa telom Tocak
Nošenje	kotrljajući lezaj
Boja Tocak	Prirodno belo
stitnici omotaca	Bez stražara
Prečnik	125 mm
Širina omotac	40 mm
dimenzija rupa osovina	12 mm
dužina glavcine	48,4 mm
Širina tela	40 mm
Teškoća gazećeg omotac (D)	75 Šor D

PERFORMANSE

Performanse kotrljanja	● ● ● ○ ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ● ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Duratech
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	300 kg
Statički Nosivost	600 kg
Temperaturni opseg (Minimalno)	-25 °C
Opseg temperature (maksimalni)	80 °C
Ukupna težina	0,272 kg

DURATECH

UOR 125X40-Ø12 HL48,4

EAN 4031582323559
Broj porudžbine 00030967



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

