

DURATECH HEAT

BOG 100X35 HL45,5 ASM.

EAN 4031582347227
Broj porudžbine 00035370



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

KUCISTE

nerdjajuci

✓

PERFORMANSE

Performanse kotrljanja ● ● ● ○ ○

Buka u pokretu ● ● ○ ○ ○

Ishrana ● ● ● ● ●

otpornost na rdju ● ● ● ● ●

OSNOVNI ATRIBUTI

Naziv proizvoda	Duratech heat
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	125 kg
Statički Nosivost	250 kg
Temperaturni opseg (Minimalno)	-40 °C
Opseg temperature (maksimalni)	280 °C
Ukupna težina	0,3 kg

TOCAK

Materijal za telo	plastika termoset, otporan na toplotu
materijal omotaca	Identično sa telom Tocak
Nošenje	grm sa suvim ležajem
Boja Tocak	Crna
Prečnik	100 mm
Širina omotac	35 mm
dimenzija rupa osovina	8 mm
duzina glavnice	45,5 mm
Širina tela	35 mm
Teškoća gazećeg omotac (D)	90 Šor D

DURATECH HEAT

BOG 100X35 HL45,5 ASM.

EAN 4031582347227

Broj porudžbine 00035370



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

