

# PURETECH

PVR 300X50-Ø20 HL58

EAN 4031582321357  
Order number 00038262



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Polypropylene
Tread material	Solid rubber, black
Bearing	Roller bearing
Wheel color	Graphite black (RAL9011)
Threadguards	Without threadguard
Diameter	300 mm
Tread width	50 mm
Axle hole diameter	20 mm
Hub length	58 mm
Body width	50 mm
Hardness of tread (A)	80 Shore A

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Puretech
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	250 kg
Load capacity Static	500 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	2.821 kg

# PURETECH

PVR 300X50-Ø20 HL58

EAN 4031582321357  
Order number 00038262



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

