

PURETECH

PVR 250X60-Ø25

EAN 4031582321340
Order number 00050608



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polypropylene
Tread material	Solid rubber, black
Bearing	Roller bearing
Wheel color	Graphite black (RAL9011)
Threadguards	Without threadguard
Diameter	250 mm
Tread width	60 mm
Axle hole diameter	25 mm
Hub length	74 mm
Body width	60 mm
Hardness of tread (A)	80 Shore A

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Puretech
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	295 kg
Load capacity Static	590 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	2.872 kg

PURETECH

PVR 250X60-Ø25

EAN 4031582321340
Order number 00050608



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

