

PURETECH

PVR 250X60-Ø25

EAN 4031582321340
Order number 00050608



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polypropylene
Tread material	Solid rubber, black
Bearing	Roller bearing
Wheel color	Graphite black (RAL9011)
Threadguards	Without threadguard
Diameter	9.84 in
Tread width	2.36 in
Axle hole diameter	0.98 in
Hub length	2.91 in
Body width	2.36 in
Hardness of tread (A)	80 Shore A

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Puretech
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	650.36 lb
Load capacity Static	1300.73 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall weight	6.33 lb

PURETECH

PVR 250X60-Ø25

EAN 4031582321340
Order number 00050608



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

