

# DURATECH

TOP 160X50-Ø20 HL60

EAN 4031582322705  
Order number 00801134



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

### WHEEL

Body material	Polyamide, heavy
Tread material	Identical with wheel body
Bearing	Precision ball bearing
Wheel color	Natural white
Threadguards	With threadguard
Diameter	6.3 in
Tread width	1.97 in
Axle hole diameter	0.79 in
Hub length	2.36 in
Body width	1.97 in
Hardness of tread (D)	75 Shore D
Bearing type	6204

### PERFORMANCE

Roll performance	● ● ● ● ●
Movement noise	● ● ○ ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

### CORE ATTRIBUTES

Product name	Duratech
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	2248.71 lb
Load capacity at 6 km/h	1873.93 lb
Load capacity Static	3747.85 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	176 °F
Overall weight	2.5 lb

# DURATECH

TOP 160X50-Ø20 HL60

EAN 4031582322705  
Order number 00801134



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

