

NOVATECH

FTP 150X60-Ø20 HL60

EAN 4031582329490

Broj porudžbine 00801150



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	Casting
materijal omotaca	Poliuretana, liveno
Nošenje	precizini kuglicni lezaj
Boja Tocak	Med žuta (RAL1005)
stitnici omotaca	Sa threadguard
Prečnik	150 mm
Širina omotac	60 mm
dimenzija rupa osovina	20 mm
dužina glavcine	60 mm
Širina tela	60 mm
Teškoća gazećeg omotac (A)	92 Šor A
Teškoća gazećeg omotac (D)	42 Šor D

PERFORMANSE

Performanse kotrljanja	● ● ● ● ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ● ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Novatech
Standard	EN12533 - Tockovi za teske terete
Nosivost na 4 km/h	960 kg
Nosivost na 6 km/h	800 kg
Statički Nosivost	1600 kg
Temperaturni opseg (Minimalno)	-10 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	3,342 kg

NOVATECH

FTP 150X60-Ø20 HL60

EAN 4031582329490
Broj porudžbine 00801150



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

