

# DURATECH

MOP 150X50-Ø30 HL60

EAN 4031582320022

Broj porudžbine 00801260



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## TOCAK

Materijal za telo	poliamid, super težak
materijal omotaca	Identično sa telom Tocak
Nošenje	precizini kuglicni lezaj
Boja Tocak	Prirodno belo
stitnici omotaca	Sa threadguard
Prečnik	150 mm
Širina omotac	50 mm
dimenzija rupa osovina	30 mm
dužina glavcine	60 mm
Širina tela	50 mm
Teškoća gazećeg omotac (D)	75 Šor D
Tip ležaja	6306

## PERFORMANSE

Performanse kotrljanja	● ● ● ● ●
Buka u pokretu	● ● ○ ○ ○
Ishrana	● ● ● ● ●
otpornost na rdju	● ● ● ○ ○

## OSNOVNI ATRIBUTI

Naziv proizvoda	Duratech
Standard	EN12533 - Tockovi za teske terete
Nosivost na 4 km/h	2520 kg
Nosivost na 6 km/h	2100 kg
Statički Nosivost	4200 kg
Temperaturni opseg (Minimalno)	-40 °C
Opseg temperature (maksimalni)	80 °C
Ukupna težina	1,446 kg

# DURATECH

MOP 150X50-Ø30 HL60

EAN 4031582320022  
Broj porudžbine 00801260



BETTER MOBILITY. BETTER LIFE.

## TEHNIČKI CRTEŽI

