

DURATECH

MOP 200X50-Ø35 HL60

EAN 4031582320053
Order number 00801262



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polyamide, super heavy
Tread material	Identical with wheel body
Bearing	Precision ball bearing
Wheel color	Natural white
Threadguards	With threadguard
Diameter	200 mm
Tread width	50 mm
Axle hole diameter	35 mm
Hub length	60 mm
Body width	50 mm
Hardness of tread (D)	75 Shore D
Bearing type	6307

PERFORMANCE

Roll performance	● ● ● ● ●
Movement noise	● ● ○ ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Duratech
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	3360 kg
Load capacity at 6 km/h	2800 kg
Load capacity Static	5600 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall weight	2.578 kg

DURATECH

MOP 200X50-Ø35 HL60

EAN 4031582320053
Order number 00801262



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

