

DURATECH

MOP 200X50-Ø35 HL60

EAN 4031582320053
Order number 00801262



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polyamide, super heavy
Tread material	Identical with wheel body
Bearing	Precision ball bearing
Wheel color	Natural white
Threadguards	With threadguard
Diameter	7.87 in
Tread width	1.97 in
Axle hole diameter	1.38 in
Hub length	2.36 in
Body width	1.97 in
Hardness of tread (D)	75 Shore D
Bearing type	6307

PERFORMANCE

Roll performance	● ● ● ● ●
Movement noise	● ● ○ ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Duratech
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	7407.52 lb
Load capacity at 6 km/h	6172.94 lb
Load capacity Static	12345.87 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	176 °F
Overall weight	5.68 lb

DURATECH

MOP 200X50-Ø35 HL60

EAN 4031582320053
Order number 00801262



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

