

## NOVATECH

FTP 250X80-Ø30 HL90

EAN 4031582319422

Broj porudžbine 00801280



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## TOCAK

Materijal za telo	Casting
materijal omotaca	Poliuretana, liveno
Nošenje	precizini kuglicni lezaj
Boja Tocak	Med žuta (RAL1005)
stitnici omotaca	Sa threadguard
Prečnik	250 mm
Širina omotac	80 mm
dimenzija rupa osovina	30 mm
dužina glavcine	90 mm
Širina tela	80 mm
Teškoća gazećeg omotac (A)	92 Šor A
Teškoća gazećeg omotac (D)	42 Šor D

## PERFORMANSE

Performanse kotrljanja	● ● ● ● ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ● ○
otpornost na rdju	● ● ● ○ ○

## OSNOVNI ATRIBUTI

Naziv proizvoda	Novatech
Standard	EN12533 - Tockovi za teske terete
Nosivost na 4 km/h	2160 kg
Nosivost na 6 km/h	1800 kg
Statički Nosivost	3600 kg
Temperaturni opseg (Minimalno)	-10 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	9,262 kg

# NOVATECH

FTP 250X80-Ø30 HL90

EAN 4031582319422  
Broj porudžbine 00801280



BETTER MOBILITY. BETTER LIFE.

## TEHNIČKI CRTEŽI

