

PRODUCT INFORMATION

NOVATECH

ITP 100X50-Ø20 HL60

EAN 4031582070309
Order number 00801297



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Aluminum
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Wheel color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	3.94 in
Tread width	1.97 in
Axle hole diameter	0.79 in
Hub length	2.36 in
Body width	1.97 in
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Novatech
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	1190.49 lb
Load capacity at 6 km/h	947.99 lb
Load capacity Static	2380.99 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	140 °F
Overall weight	1.37 lb

NOVATECH

ITP 100X50-Ø20 HL60

EAN 4031582070309
Order number 00801297



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

