

## NOVATECH

ITP 100X50-Ø20 HL60

EAN 4031582070309

Broj porudžbine 00801297



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## TOCAK

Materijal za telo	Aluminijum
materijal omotaca	Poliuretana, liveno
Nošenje	precizini kuglicni lezaj
Boja Tocak	Med žuta (RAL1005)
stitnici omotaca	Sa threadguard
Prečnik	100 mm
Širina omotac	50 mm
dimenzija rupa osovina	20 mm
dužina glavcine	60 mm
Širina tela	50 mm
Teškoća gazećeg omotac (A)	92 Šor A
Teškoća gazećeg omotac (D)	42 Šor D

## PERFORMANSE

Performanse kotrljanja	● ● ● ● ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ● ○
otpornost na rdju	● ● ● ○ ○

## OSNOVNI ATRIBUTI

Naziv proizvoda	Novatech
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	540 kg
Nosivost na 6 km/h	430 kg
Statički Nosivost	1080 kg
Temperaturni opseg (Minimalno)	-10 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	0,62 kg

# NOVATECH

ITP 100X50-Ø20 HL60

EAN 4031582070309  
Broj porudžbine 00801297



BETTER MOBILITY. BETTER LIFE.

## TEHNIČKI CRTEŽI

