

PRODUCT INFORMATION

NOVATECH

FTP 250X100-Ø35 HL120

EAN 4031582319361  
Order number 00801911



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Casting
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Wheel color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	9.84 in
Tread width	3.94 in
Axle hole diameter	1.38 in
Hub length	4.72 in
Body width	3.94 in
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Novatech
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	5820.2 lb
Load capacity at 6 km/h	4850.16 lb
Load capacity Static	9700.33 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	140 °F
Overall weight	33.2 lb

# NOVATECH

FTP 250X100-Ø35 HL120

EAN 4031582319361  
Order number 00801911



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

