

PRODUCT INFORMATION

NOVATECH

STP 500X100-Ø50 HL120

EAN 4031582322279  
Order number 00801916



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Sheet steel, heavy
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Wheel color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	500 mm
Tread width	100 mm
Axle hole diameter	50 mm
Hub length	120 mm
Body width	100 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Novatech
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	4800 kg
Load capacity at 6 km/h	4000 kg
Load capacity Static	8000 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	60 °C
Overall weight	50.507 kg

# NOVATECH

STP 500X100-Ø50 HL120

EAN 4031582322279  
Order number 00801916



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

