

NOVATECH

STP 250X100-Ø35 HL120

EAN 4031582322231

Broj porudžbine 00802281



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	Čelik od limova, težak
materijal omotaca	Poliuretana, liveno
Nošenje	precizini kuglicni lezaj
Boja Tocak	Med žuta (RAL1005)
stitnici omotaca	Sa threadguard
Prečnik	250 mm
Širina omotac	100 mm
dimenzija rupa osovina	35 mm
dužina glavcine	120 mm
Širina tela	100 mm
Teškoća gazećeg omotac (A)	92 Šor A
Teškoća gazećeg omotac (D)	42 Šor D

PERFORMANSE

Performanse kotrljanja	● ● ● ● ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ● ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Novatech
Standard	EN12533 - Tockovi za teske terete
Nosivost na 4 km/h	2640 kg
Nosivost na 6 km/h	2200 kg
Statički Nosivost	4400 kg
Temperaturni opseg (Minimalno)	-10 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	18,321 kg

NOVATECH

STP 250X100-Ø35 HL120

EAN 4031582322231
Broj porudžbine 00802281



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

