

PRODUCT INFORMATION

NOVATECH

FTP 400X80-Ø40 HL90

EAN 4031582319507  
Order number 00802486



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Casting
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Wheel color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	15.75 in
Tread width	3.15 in
Axle hole diameter	1.57 in
Hub length	3.54 in
Body width	3.15 in
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Novatech
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	6613.86 lb
Load capacity at 6 km/h	5511.55 lb
Load capacity Static	11023.1 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	140 °F
Overall weight	52.02 lb

# NOVATECH

FTP 400X80-Ø40 HL90

EAN 4031582319507  
Order number 00802486



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

