

NOVATECH

FTP 400X80-Ø40 HL90

EAN 4031582319507

Broj porudžbine 00802486



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	Casting
materijal omotaca	Poliuretana, liveno
Nošenje	precizini kuglicni lezaj
Boja Tocak	Med žuta (RAL1005)
stitnici omotaca	Sa threadguard
Prečnik	400 mm
Širina omotac	80 mm
dimenzija rupa osovina	40 mm
dužina glavcine	90 mm
Širina tela	80 mm
Teškoća gazećeg omotac (A)	92 Šor A
Teškoća gazećeg omotac (D)	42 Šor D

PERFORMANSE

Performanse kotrljanja	● ● ● ● ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ● ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Novatech
Standard	EN12533 - Tockovi za teske terete
Nosivost na 4 km/h	3000 kg
Nosivost na 6 km/h	2500 kg
Statički Nosivost	5000 kg
Temperaturni opseg (Minimalno)	-10 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	23,598 kg

NOVATECH

FTP 400X80-Ø40 HL90

EAN 4031582319507
Broj porudžbine 00802486



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

