

# DURATECH

TOP 200X50-Ø25 HL60

EAN 4031582322736  
Order number 00802937



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

### WHEEL

|                       |                           |
|-----------------------|---------------------------|
| Body material         | Polyamide, heavy          |
| Tread material        | Identical with wheel body |
| Bearing               | Precision ball bearing    |
| Wheel color           | Natural white             |
| Threadguards          | With threadguard          |
| Diameter              | 7.87 in                   |
| Tread width           | 1.97 in                   |
| Axle hole diameter    | 0.98 in                   |
| Hub length            | 2.36 in                   |
| Body width            | 1.97 in                   |
| Hardness of tread (D) | 75 Shore D                |
| Bearing type          | 6205                      |

### PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ● ● |
| Movement noise       | ● ● ○ ○ ○ |
| Attrition            | ● ● ● ● ● |
| Corrosion resistance | ● ● ● ○ ○ |

### CORE ATTRIBUTES

|                             |                              |
|-----------------------------|------------------------------|
| Product name                | Duratech                     |
| Standard                    | EN12533 - Heavy Duty Castors |
| Load capacity at 4 km/h     | 2645.54 lb                   |
| Load capacity at 6 km/h     | 2204.62 lb                   |
| Load capacity Static        | 3527.39 lb                   |
| Temperature range (Minimum) | -40 °F                       |
| Temperature range (Maximum) | 176 °F                       |
| Overall weight              | 3.53 lb                      |

# DURATECH

TOP 200X50-Ø25 HL60

EAN 4031582322736  
Order number 00802937



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

