

NOVATECH

FTP 200X60-Ø25 HL60

EAN 4031582329674
Order number 00803012



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

| | |
|-----------------------|------------------------|
| Body material | Casting |
| Tread material | Polyurethane, casted |
| Bearing | Precision ball bearing |
| Wheel color | Honey yellow (RAL1005) |
| Threadguards | With threadguard |
| Diameter | 200 mm |
| Tread width | 60 mm |
| Axle hole diameter | 25 mm |
| Hub length | 60 mm |
| Body width | 60 mm |
| Hardness of tread (A) | 92 Shore A |
| Hardness of tread (D) | 42 Shore D |

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ● ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|------------------------------|
| Product name | Novatech |
| Standard | EN12533 - Heavy Duty Castors |
| Load capacity at 4 km/h | 1440 kg |
| Load capacity at 6 km/h | 1200 kg |
| Load capacity Static | 2400 kg |
| Temperature range (Minimum) | -10 °C |
| Temperature range (Maximum) | 60 °C |
| Overall weight | 5.347 kg |

NOVATECH

FTP 200X60-Ø25 HL60

EAN 4031582329674
Order number 00803012



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

