

NOVATECH

FTP 200X60-Ø25 HL60

EAN 4031582329674

Broj porudžbine 00803012



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	Casting
materijal omotaca	Poliuretana, liveno
Nošenje	precizini kuglicni lezaj
Boja Tocak	Med žuta (RAL1005)
stitnici omotaca	Sa threadguard
Prečnik	200 mm
Širina omotac	60 mm
dimenzija rupa osovina	25 mm
dužina glavcine	60 mm
Širina tela	60 mm
Teškoća gazećeg omotac (A)	92 Šor A
Teškoća gazećeg omotac (D)	42 Šor D

PERFORMANSE

Performanse kotrljanja	● ● ● ● ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ● ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Novatech
Standard	EN12533 - Tockovi za teske terete
Nosivost na 4 km/h	1440 kg
Nosivost na 6 km/h	1200 kg
Statički Nosivost	2400 kg
Temperaturni opseg (Minimalno)	-10 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	5,347 kg

NOVATECH

FTP 200X60-Ø25 HL60

EAN 4031582329674
Broj porudžbine 00803012



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

