

PRODUCT INFORMATION

NOVATECH

STP 500X150-Ø50 HL160

EAN 4031582322286
Order number 00803302



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Sheet steel, heavy
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Wheel color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	500 mm
Tread width	150 mm
Axle hole diameter	50 mm
Hub length	160 mm
Body width	150 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Novatech
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	6360 kg
Load capacity at 6 km/h	5300 kg
Load capacity Static	10600 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	60 °C
Overall weight	62.353 kg

NOVATECH

STP 500X150-Ø50 HL160

EAN 4031582322286
Order number 00803302



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

