

# NOVATECH

ITP 250X55-Ø25 HL60

EAN 4031582319934  
Order number 00827859



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Aluminum
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Wheel color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	9.84 in
Tread width	2.17 in
Axle hole diameter	0.98 in
Hub length	2.36 in
Body width	2.17 in
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

## PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Novatech
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	2204.62 lb
Load capacity at 6 km/h	1763.7 lb
Load capacity Static	4409.24 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	140 °F
Overall weight	5.11 lb

# NOVATECH

ITP 250X55-Ø25 HL60

EAN 4031582319934  
Order number 00827859



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

