

NOVATECH

ITP 250X55-Ø25 HL60

EAN 4031582319934

Broj porudžbine 00827859



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	Aluminijum
materijal omotaca	Poliuretana, liveno
Nošenje	precizini kuglicni lezaj
Boja Tocak	Med žuta (RAL1005)
stitnici omotaca	Sa threadguard
Prečnik	250 mm
Širina omotac	55 mm
dimenzija rupa osovina	25 mm
dužina glavcine	60 mm
Širina tela	55 mm
Teškoća gazećeg omotac (A)	92 Šor A
Teškoća gazećeg omotac (D)	42 Šor D

PERFORMANSE

Performanse kotrljanja	● ● ● ● ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ● ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Novatech
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	1000 kg
Nosivost na 6 km/h	800 kg
Statički Nosivost	2000 kg
Temperaturni opseg (Minimalno)	-10 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	2,316 kg

NOVATECH

ITP 250X55-Ø25 HL60

EAN 4031582319934
Broj porudžbine 00827859



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

