

NOVATECH

STP 500X80-Ø50 HL90

EAN 4031582322293
Order number 00830812



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Sheet steel, heavy
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Wheel color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	500 mm
Tread width	80 mm
Axle hole diameter	50 mm
Hub length	90 mm
Body width	80 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Novatech
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	3840 kg
Load capacity at 6 km/h	3200 kg
Load capacity Static	6400 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	60 °C
Overall weight	40.634 kg

NOVATECH

STP 500X80-Ø50 HL90

EAN 4031582322293
Order number 00830812



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

