

PRODUCT INFORMATION

NOVATECH

STP 500X80-Ø50 HL90

EAN 4031582322293
Order number 00830812



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

| | |
|-----------------------|------------------------|
| Body material | Sheet steel, heavy |
| Tread material | Polyurethane, casted |
| Bearing | Precision ball bearing |
| Wheel color | Honey yellow (RAL1005) |
| Threadguards | With threadguard |
| Diameter | 19.69 in |
| Tread width | 3.15 in |
| Axle hole diameter | 1.97 in |
| Hub length | 3.54 in |
| Body width | 3.15 in |
| Hardness of tread (A) | 92 Shore A |
| Hardness of tread (D) | 42 Shore D |

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ● ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|------------------------------|
| Product name | Novatech |
| Standard | EN12533 - Heavy Duty Castors |
| Load capacity at 4 km/h | 8465.74 lb |
| Load capacity at 6 km/h | 7054.78 lb |
| Load capacity Static | 14109.57 lb |
| Temperature range (Minimum) | 14 °F |
| Temperature range (Maximum) | 140 °F |
| Overall weight | 89.58 lb |

NOVATECH

STP 500X80-Ø50 HL90

EAN 4031582322293
Order number 00830812



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

