

## NOVATECH

STP 500X80-Ø50 HL90

EAN 4031582322293

Broj porudžbine 00830812



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## TOCAK

Materijal za telo	Čelik od limova, težak
materijal omotaca	Poliuretana, liveno
Nošenje	precizini kuglicni lezaj
Boja Tocak	Med žuta (RAL1005)
stitnici omotaca	Sa threadguard
Prečnik	500 mm
Širina omotac	80 mm
dimenzija rupa osovina	50 mm
dužina glavcine	90 mm
Širina tela	80 mm
Teškoća gazećeg omotac (A)	92 Šor A
Teškoća gazećeg omotac (D)	42 Šor D

## PERFORMANSE

Performanse kotrljanja	● ● ● ● ○
Buka u pokretu	● ● ● ● ○
Ishrana	● ● ● ● ○
otpornost na rdju	● ● ● ● ○

## OSNOVNI ATRIBUTI

Naziv proizvoda	Novatech
Standard	EN12533 - Tockovi za teske terete
Nosivost na 4 km/h	3840 kg
Nosivost na 6 km/h	3200 kg
Statički Nosivost	6400 kg
Temperaturni opseg (Minimalno)	-10 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	40,634 kg

# NOVATECH

STP 500X80-Ø50 HL90

EAN 4031582322293

Broj porudžbine 00830812



BETTER MOBILITY. BETTER LIFE.

## TEHNIČKI CRTEŽI

