

NOVATECH

ITP 100X40-Ø12 HL45 INCL. A-SET

EAN 4031582070293
Order number 00830827



Image may differ from the original product

WHEEL

Body material	Aluminium
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Wheel color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	100 mm
Tread width	40 mm
Axle hole diameter	12 mm
Hub length	45 mm
Body width	40 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Novatech
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	300 kg
Load capacity at 6 km/h	240 kg
Load capacity Static	600 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	60 °C
Overall weight	0.502 kg

NOVATECH

ITP 100X40-Ø12 HL45 INCL. A-SET

EAN 4031582070293
Order number 00830827



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

