

AGILA

2470PJO075P30-11

EAN 4031582010398
Order number 00003349



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ● ○ |
| Attrition | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|---------------------------|
| Product name | Agila |
| Housing type | Swivel castor |
| Standard | EN12530 - Devices Castors |
| Load capacity at 3 km/h | 75 kg |
| Load capacity Static | 150 kg |
| Temperature range (Minimum) | -20 °C |
| Temperature range (Maximum) | 60 °C |
| Overall height | 100 mm |
| Overall width | 43 mm |
| Overall weight | 0.211 kg |

WHEEL

| | |
|-----------------------|-----------------------|
| Body material | Polypropylene |
| Tread material | Thermoplastic rubber |
| Bearing | Plain bearing |
| Wheel color | Silver grey (RAL7001) |
| Threadguards | Without threadguard |
| Diameter | 75 mm |
| Tread width | 25 mm |
| Body width | 25 mm |
| Hardness of tread (A) | 87 Shore A |

HOUSING

| | |
|---------------------|---------------------|
| Material | Steel sheet, medium |
| Fork shape | Broad |
| Swivel bearing | Two ball races |
| Colour | Blue passivated |
| Offset | 24 mm |
| Swivel radius | 61.5 mm |
| Swivel interference | 123 mm |
| Dome diameter | 43 mm |

FITTING

| | |
|--------------------|--|
| Fitting type | Bolt hole |
| Bolt hole diameter | 11 mm |
| Hint | Castors can be mounted with standard screws of any length. |

AGILA

2470PJO075P30-11

EAN 4031582010398
Order number 00003349



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

