

# AGILA TWIN

2977PJP075P50

EAN 4031582302943  
Order number 00003591



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ● ○ |
| Attrition            | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product name                | Agila twin                    |
| Housing type                | Swivel castor with total lock |
| Standard                    | EN12530 - Devices Castors     |
| Load capacity at 3 km/h     | 100 kg                        |
| Load capacity Static        | 200 kg                        |
| Temperature range (Minimum) | -20 °C                        |
| Temperature range (Maximum) | 60 °C                         |
| Overall height              | 102 mm                        |
| Overall width               | 71 mm                         |
| Overall weight              | 0.742 kg                      |

## WHEEL

|                       |                        |
|-----------------------|------------------------|
| Body material         | Polypropylene          |
| Tread material        | Thermoplastic rubber   |
| Bearing               | Precision ball bearing |
| Wheel color           | Silver grey (RAL7001)  |
| Threadguards          | With threadguard       |
| Diameter              | 75 mm                  |
| Tread width           | 25 mm                  |
| Body width            | 25 mm                  |
| Hardness of tread (A) | 87 Shore A             |

## HOUSING

|                     |                     |
|---------------------|---------------------|
| Material            | Steel sheet, medium |
| Fork shape          | Twin wheel housing  |
| Swivel bearing      | Two ball races      |
| Colour              | Blue passivated     |
| Offset              | 31.3 mm             |
| Swivel radius       | 99 mm               |
| Swivel interference | 198 mm              |
| Dome diameter       | 65 mm               |

## FITTING

|                             |                   |
|-----------------------------|-------------------|
| Fitting type                | Rectangular plate |
| Plate length                | 77 mm             |
| Plate width                 | 67 mm             |
| Plate hole length (Minimum) | 46.5 mm           |
| Plate hole length (Maximum) | 51.5 mm           |
| Plate hole width (Minimum)  | 56 mm             |
| Plate hole width (Maximum)  | 61.5 mm           |
| Plate hole diameter         | 8.5 mm            |

# AGILA TWIN

2977PJP075P50

EAN 4031582302943  
Order number 00003591



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

