

AGILA

2478DIK050P41-55

EAN 4031582030037
Order number 00003897



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ● ○ |
| Attrition | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|---------------------------|
| Product name | Agila |
| Housing type | Fixed castor |
| Standard | EN12530 - Devices Castors |
| Load capacity at 3 km/h | 40 kg |
| Load capacity Static | 80 kg |
| Temperature range (Minimum) | -20 °C |
| Temperature range (Maximum) | 85 °C |
| Overall height | 69 mm |
| Overall width | 35 mm |
| Overall weight | 0.157 kg |

WHEEL

| | |
|-----------------------|---------------------------|
| Body material | Sheet Steel |
| Tread material | Solid rubber, non-marking |
| Bearing | Cone ball bearing |
| Wheel color | Blue passivated |
| Threadguards | With threadguard |
| Diameter | 50 mm |
| Tread width | 19 mm |
| Body width | 19 mm |
| Hardness of tread (A) | 80 Shore A |

HOUSING

| | |
|---------------|---------------------|
| Material | Steel sheet, medium |
| Fork shape | Broad |
| Colour | Blue passivated |
| Dome diameter | 27 mm |

FITTING

| | |
|-----------------------------|--------------|
| Fitting type | Square plate |
| Plate length | 55 mm |
| Plate width | 55 mm |
| Plate hole length (Minimum) | 38.5 mm |
| Plate hole length (Maximum) | 44 mm |
| Plate hole width (Minimum) | 38.5 mm |
| Plate hole width (Maximum) | 44 mm |
| Plate hole diameter | 6.3 mm |

AGILA

2478DIK050P41-55

EAN 4031582030037
Order number 00003897



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

